



Cable Datasheet

RS Stock Number	811-4598
Conductors	32/0.20mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation	PVC (Type TI1 to BS 7655)
Insulation Radial	0.6mm
Thickness Diameter over	2.52mm (Nominal)
Insulation Number of	5
Cores	Blue, Brown, Black, Grey & Green/Yellow
Core Colours	
Sheath	PVC (Type TM2 to BS 7655)
Sheath radial thickness	0.9mm
Overall Dimensions	8.6mm (Nominal)
Voltage Rating	300/500V
Conductor Resistance	19.5Ω/km at 20°C (nominal)
Cable Weight	106kg/km (nominal)
Standards	BS EN 50525-2-11 Clause 4.2
Harmonization Code	H05VV-F
Sheath Colour	White
Reel Length	100m