



Sample photo

Order symbol: AL 314011
Product nbr: 7011450
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004291
El. number:
Finland: 3423645
Denmark: 8212004867
Italy: 7321120

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		403	310	110	Ingress Protection (EN 60529): IP 66/67
inch:		15.9	12.2	4.3	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:		Aluminium			Certificates: Underwriters Laboratories Fimko UL Canada Gost R
Base colour:		RAL 7001			
Cover colour:		RAL 7001			
Cover screws material:		Stainless steel			
Gasket material:		Neoprene			
Temperatures:					
Short term:		-50 ... 140 °C			
Continuous:		-50 ... 80 °C			
Short term:		-60 ... 285 °F			
Continuous:		-60 ... 175 °F			
Accessories:					
AM 3140		Mounting plate			
ARH 40		DIN-35 Mounting rail			
MRS 28541		Wall fastening lug (2 pcs)			
PH A & AH A/B		Hinge set			

