



iM2750

Large Case

Travel Case



- Four Press & Pull Latches
- Four Press & Pull Latches
 - Three Double-layered, Soft-grip Handles
 - Two Padlockable Hasps
 - In-line Wheels
 - Telescoping Handle
 - Vortex® Valve
 - Flush Powerful Hinges
 - Lightweight Strong HPX® Resin
 - Watertight
 - Peli's limited lifetime guarantee**
 - Peli's limited lifetime guarantee****Where applicable by law
 - **Where applicable by law

CONFIGURATIONS

- iM2750** - Standard
- iM2750-X0000** - With No Foam
- iM2750-X0002** - With With Padded Dividers

DIMENSIONS

- Interior (L x W x D):** 22.00 x 17.00" x 12.70 (55.9 x 43.2 x 32.3 cm)
- Exterior (L x W x D):** 24.60 x 19.70" x 14.40 (62.5 x 50 x 36.6 cm)
- Lid Depth:** 2.00"
- Bottom Depth:** 10.70"
- Total Depth:** 12.7"
- Int Volume:** 2.75 ft³

MATERIALS

- Body:** Injection Molded HPX® high performance resin
- Latch:** Valox - Polybutylene Terephthalate (PBT)
- Latch (Alt):** Xenoy - Polyester/Polycarbonate blend
- O-Ring:** Silicone Sponge
- Pins:** Stainless Steel
- Pins (Alt):** Aluminum
- Foam:** 1.3/1.35 polyester
- Purge Body:** Valox - Polybutylene Terephthalate (PBT)
- Purge Body (Alt):** Xenoy - Polyester/Polycarbonate blend
- Purge Vent:** Gortex membrane
- Purge O-Ring:** Buna-N, 50-60 Durometer Shore A

COLOURS



Black



Yellow



OD Green

WEIGHT

Weight With Foam: 23.40 lbs

Weight Without Foam: 18.50 lbs

Buoyancy: 173.40 lbs

Master Pack Weight: 25.20 lbs

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

FOAM PROPERTIES

Layer 1 (Lid): 2.00" Convolute

Layer 2 (Base): 0.63" Pad

Layer 3 (Base): 1.69" Pick N Pluck

Layer 4 (Base): 1.69" Pick N Pluck

Layer 5 (Base): 1.69" Pick N Pluck

Layer 6 (Base): 1.69" Pick N Pluck

Layer 7 (Base): 1.69" Pick N Pluck

OTHER

Extendable Handle: yes

Master Pack: 1

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com