

Datasheet

RS Pro Stainless Steel Abrasive End Brush, 12000rpm, 19mm Diameter

RS Stock No: **374-856**



Product Details

RS Pro stainless steel abrasive end brush with bristle, has a diameter of 19 mm and shaft diameter of 6 mm. It is perfect for cleaning or deburring hard to reach areas and is available in mild steel wire or stainless steel wire. The steel wire version is identified by green mark on cup section.

Features and Benefits

- Stainless steel bristle construction
- 12000 rpm maximum safe speed
- Shank fixing type
- 31 mm long bristle



ENGLISH

Specifications:

Bristle Material	Stainless Steel
Fixing Type	Shank
Bristle Length	31 mm
Diameter	19 mm
Fixing Size	6 mm
Maximum Safe Speed	12000 rpm
Number of Pieces	6
Suitable For	Roughening, Deburring, Planning, Edge Honing, Structuring, Descaling/Paint Stripping & Weld Seams
Type	102 P