


Grommet - HC-D 15-PR-DI - 1661189

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Replacement profile gasket for HC-D15 sleeve housing



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 155551
Weight per Piece (excluding packing)	1.03 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

General

Material	NBR
Assembly instructions	Profile gasket must be glued to the housing, not for ADVANCE housings, not for HC-...EMC housings.

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

Grommet - HC-D 15-PR-DI - 1661189

Classifications

eCl@ss

eCl@ss 8.0	27440209
------------	----------

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC001121
ETIM 4.0	EC001181
ETIM 5.0	EC001181

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals


Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Drawings

Grommet - HC-D 15-PR-DI - 1661189

