

70 - 295kg Wheels for Industrial Castors

Load capacity tested according EN 12532

		Wheel diameter [mm]	Width of Tread [mm]	Axle Hole-Ø [mm]	Hub length [mm]			Load capacity [kg]	Express / On Stock	Order number	EAN Code
PVO	Description										
	Wheel centre:	80	35	12	44,4		70		PVO080x35-Ø12	4031582321180	
	Polypropylene, black,	100	35	12	44,4		75		PVO100x35-Ø12	4031582321197	
	Tread: solid rubber, black,	125	37	12	44,4		100		PVO125x37-Ø12	4031582321203	
	plain bearing, temperature	160	40	20	58		135		PVO160x40-Ø20	4031582321210	
	range from - 20 to + 60 °C	200	50	20	58		205		PVO200x50-Ø20	4031582321227	
PVR/PVL	Description								Order number	EAN Code	
	Wheel centre:	80	35	12	44,4		70		PVR080x35-Ø12	4031582321241	
	Polypropylene, black,	100	35	12	44,4		75		PVR100x35-Ø12	4031582321258	
	Tread: solid rubber, black,	125	37	12	44,4		100		PVR125x37-Ø12 HL44,4	4031582321265	
	PVR: roller bearing,	125	37	12	48		100		PVR125x37-Ø12 HL48	4031582321272	
	PVL: roller bearing with	125	37	15	58		100		PVR125x37-Ø15	4031582321289	
	spacer, temperature range	160	40	20	58		135		PVR160x40-Ø20	4031582321296	
	from - 20 to + 60 °C	200	50	20	58		205		PVR200x50-Ø20	4031582321302	
		200	50	25	58		205		PVR200x50-Ø25	4031582321319	
	250	60	25	74		295		PVR250x60-Ø25	4031582321340		
	300	50	20	58		250		PVR300x50-Ø20	4031582321357		
PIO	Description								Order number	EAN Code	
	Wheel centre:	80	35	12	44,4		70		PIO080x35-Ø12	4031582399288	
	Polypropylene, Tread: solid	100	35	12	44,4		75		PIO100x35-Ø12	4031582399295	
	rubber, grey, non-marking,	125	37	12	44,4		100		PIO125x37-Ø12	4031582399301	
	without threadguards,	160	40	20	58		135		PIO160x40-Ø20	4031582399318	
	plain bearing, temperature	200	50	20	58		205		PIO200x50-Ø20	4031582399325	
range from - 20 to + 60 °C											
PIR grey, non-marking	Description								Order number	EAN Code	
	Wheel centre:	80	35	12	44,4		70		PIR080x35-Ø12	4031582370713	
	Polypropylene, black,	100	35	12	44,4		75		PIR100x35-Ø12 HL44,4	4031582320336	
	Tread: solid rubber, grey,	125	37	12	44,4		100		PIR125x37-Ø12 HL44,4	4031582320343	
	non-marking, roller	125	37	12	48		100		PIR125x37-Ø12 HL48	4031582320350	
	bearing, temperature range	125	37	15	58		100		PIR125x37-Ø15	4031582320367	
	from - 20 to + 60 °C	160	40	20	58		135		PIR160x40-Ø20	4031582320374	
		200	50	20	58		205		PIR200x50-Ø20	4031582320381	