

## General Information

Extended Product Type:	OHY80J6
Product ID:	1SCA022381R0410
EAN:	6417019124193
Catalog Description:	Handle OHY80J6
Long Description:	IP65, NEMA 1, 3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON- position. Screw fixing from the back side of the handle. No screws on the front ensures double insulation. The type and the ordering numbers are for one piece, red-yellow.

## Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

## Ordering

EAN:	6417019124193
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85389099

## Dimensions

Product Net Width:	113 mm
Product Net Height:	66 mm
Product Net Depth:	45 mm
Product Net Weight:	0.12 kg

## Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	80 mm
Package Level 1 Height:	66 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.12 kg
Package Level 1 EAN:	6417019124193

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

## Additional Information

Handle Length:	80 mm
Handle Type:	Pistol
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHY80
Product Name:	HANDLE
Suitable For:	OT200_...315_
Suitable for Product Class:	Switch disconnectors

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
Declaration of Conformity - CE:	1SCC390030D0203

## Classifications

ETIM 5.0:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

