






LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
FT	47				G	REDRAWN & REV PER ECN BD3869	07/29/91
					H	ADDED -3 PER NPR 4692	04/15/93
					J	REV PER EC 0320-137-97	7-29-97

1. WIRE RANGE 18-16 AWG.
2. COLOR CODED BLUE IN SPRING DIMPLE AREA.
3. 0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] MIN GOLD PER MIL-G-45204 ON INSULATION SUPPORT BARREL OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.



		PACKAGING TYPE		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13[.005] 3 PLC DEC ± - ANGLES ± -	DR 7-29-91 R.SHIREY	AMP AMP Incorporated Harrisburg, PA 17105-3608			
	CHK 9-19-91 R.STONE				
	MATERIAL	APPD 9-20-91 J.WESTMAN	NAME SOCKET ASSEMBLY, LOOSE PIECE, TYPE III+		
SEE CALLOUTS	APPD 9-23-91 W.PARKER				
	PRODUCT SPEC -				
FINISH SEE CALLOUTS	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO 66181	
	WEIGHT -	SCALE 8:1			
				SHEET	1 OF 1