






D





34POS(X-KEY):1-1903128-7





32POS(X-KEY):1-1903128-6

C



B



A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 純
mm

MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH 仕上

DWN
M. MAEBASHI
CHK
T. KUDO
APVD
D. MITSUGI

17APR2006
17APR2006
17APR2006

PRODUCT SPEC
108-78268,78298
APPLICATION SPEC
114-5377
WEIGHT

CUSTOMER DRAWING

TE Connectivity

DYNAMIC DII00D 2.0mm PITCH
TAB HSG, PANEL MOUNT TYPE
22-40 POS

SIZE
A200779

CAGE CODE
C-1903128


RESTRICTED TO

SCALE
4:1

SHEET
2

OF
3

REV
C1



REVISIONS				DATE	DWN	APVD
REV	DESCRIPTION					
1	SEE SHEET 1	-	-	-	-	-

LOC	DIST	P	LTR	DESCRIPTION	DATE	DWN	APVD
J		-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		2006	
COPYRIGHT 2006		ALL RIGHTS RESERVED.			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 17APR2006	 TE Connectivity		
DIMENSIONS: 単位: 純		CHK T. KUDO 17APR2006			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MITSUGI 17APR2006	NAME DYNAMIC D1100D 2.0mm PITCH TAB HSG, PANEL MOUNT TYPE 22-40 POS		
一般公差 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-78268,78298			
ANGLES FINISH 仕上		APPLICATION SPEC 取付適用規格 114-5377	SIZE A200779C-1903128		
MATERIAL 材料		WEIGHT			
		CUSTOMER DRAWING	RESTRICTED TO		
		SCALE 4:1	SHEET 3 OF 3		