


KEMET Part Number: LDBCA1330GC5N0
(DBCA1330GC5N0)

LDB, Film, Metallized PPS Stacked, General Purpose, 3300 pF, 2%, 50 VDC, 125°C, 1206, 1.1mm



Dimensions

Chip Size	1206
L	3.3mm +0.3/-0.1mm
W	1.7mm +/-0.2mm
T	1.1mm MAX
B	0.5mm +0.5/-0.3mm

Packaging Specifications

Packaging:	T&R
Packaging Quantity:	3000

General Information

Supplier:	KEMET
Series:	LDB
Dielectric:	Metallized PPS Stacked
Style:	SMD Chip
RoHS:	Yes
Shelf Life:	104 Weeks
MSL:	3

Specifications

Capacitance:	3300 pF
Capacitance Tolerance:	2%
Voltage DC:	50 VDC
Temperature Range:	-55/+125C
Rated Temperature:	125°C
Dissipation Factor:	0.60% 1kHz
Insulation Resistance:	3 GOhms