

FatMax®



FatMax® Flared

- ➔ Large diameter handle offers great torque needed for driving wood screws
- ➔ Colour coded ends make it easy to identify the correct screwdriver for each screw type
- ➔ Smooth domed end for fast spinning action – speed and comfort
- ➔ Shot blasted tips ensure improved torque and corrosion protection
- ➔ Soft grip handle – perfect combination of great grip plus reduces fatigue
- ➔ Chrome vanadium steel bar allows for high torque and reduces the chance of tip breakage
- ➔ Handle moulded direct to bar virtually unbreakable bond - Highly reliable and providing an extra long life

STANLEY	<u>65-016</u>	<u>65-098</u>	<u>65-137</u>
Standard tip width (mm)	4	5.5	8
Blade length (mm)	100	100	150
STANLEY	<u>65-138</u>	<u>65-139</u>	<u>65-141</u>
Standard tip width (mm)	8	10	6.5
Blade length (mm)	175	200	150
STANLEY	<u>65-143</u>	<u>65-477</u>	<u>65-478</u>
Standard tip width (mm)	12	2.5	2.5
Blade length (mm)	250	50	75
STANLEY	<u>65-479</u>	<u>65-480</u>	<u>65-481</u>
Standard tip width (mm)	3	3	4
Blade length (mm)	75	100	125
STANLEY	<u>65-482</u>	<u>65-483</u>	
Standard tip width (mm)	5.5	5.5	
Blade length (mm)	125	150	