



Product Information

FTX150x50-Ø12 NL65

EAN 4031582332063

Wheel diameter	150 mm
Width of Tread	50 mm
Axle Hole Ø	12 mm
Hub length	65 mm
Temperature	- 20 / + 60 °C
Standard	EN 12533
Hardness of tread	A 92 Shore

