



Sample photo

Order symbol: EKJB 130 G
Product nbr: 2538013
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013484
El. number:
Finland: 3425406
Electric No. Italy: 7501020
Electric No. Sweden: 2538013

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Accessories:	
mm:		280	190	130	EKJ 30-G	Cover
inch:		11.0	7.5	5.1	EKJ 80-G	Cover
					EKJ 30-T	Cover
					EKJ 80-T	Cover
					EKJVT	Mounting plate
					EKJXT	Mounting plate isolated
					EKV 12	DIN-35 Mounting rail
					EKV 22	DIN-35 Mounting rail
					EKJZR	Extension frame
Materials:						
Material:		Polycarbonate				
Base colour:		RAL 7035 -light grey				
Cover screws material:		Polyamide				
Cover colour:		RAL 7035 -light grey				
Cover screws colour:		Grey				
Gasket material:		Polyurethane				
Temperatures:						
Temperature °C (short term):		-40 ... 120 °C				
Temperature °C (continuous):		-40 ... 80 °C				
Temperature °F (short term):		-40 ... 250 °F				
Temperature °F (continuous):		-40 ... 175 °F				
Accessories:						
EKJB		Base, PC				
Rating:						
Ingress Protection (EN 60529): IP66/IP67						
Impact Resistance (EN 62262): IK08						
Electrical insulation: Totally insulated						
Halogen free (DIN/VDE 0472, Part 815): 1						
UV resistance: UL 508						
Flammability Rating: UL 746C 5"						
Glow Wire Test (IEC 695-2-1) °C: 960						
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12						
Certificates:						
SGS Fimko						
Gost R						

