

## Support rollers with axial guidance



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	C	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>			
mm			kN		kN	kN		r/min	kg	-
47	20	24	14,7	24,5	2,9	23,6	33,5	3000	0,25	NATR 20 PPA

