

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




The local bus device has digital inputs and outputs. Functions: 8 digital inputs, 3 ms filter time, 8 digital outputs of 500 mA each, 500 kbaud/2 Mbaud selection, channel-specific diagnostics, short-circuit and overload protection, M12 fast connection technology.

Why buy this product

- Flexible power supply concept
- Short-circuit and overload protection
- Diagnostic and status indicators
- SPEEDCON fast locking system
- Consistent connection via M12 connectors

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 135603
Weight per Piece (excluding packing)	319.34 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Dimensions

Width	70 mm
Height	178 mm
Depth	50 mm
Drill hole spacing	168 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (storage/transport)	95 %
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Degree of protection	IP65/67

General

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Technical data

General

Weight	330 g
Mounting type	Wall mounting
Protection class	III, IEC 61140, EN 61140, VDE 0140-1
Test section	To I/O 500 V AC

Interfaces

Name	Fieldline local bus
Connection method	M12 connector, B-coded
Designation connection point	Copper cable
Transmission speed	500 kBit/s / 2 MBit/s
Number of positions	5

Power supply for module electronics

Connection method	M12 connector
Name	U_L
Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC IEC 61131-2 (including ripple)

Fieldline potentials

Voltage supply U_L	24 V DC
Power supply at U_L	max. 4 A
Current consumption from U_L	max. 55 mA (At 2 Mbaud)
	typ. 50 mA (At 2 Mbaud)
	max. 50 mA (At 500 kBaud)
	typ. 40 mA (At 500 kBaud)
Voltage supply U_S	24 V DC
Power supply at U_S	max. 4 A
Current consumption from U_S	typ. 5 mA (plus power supply for sensors)
	max. 600 mA
Voltage supply U_{A11}	24 V DC
Power supply at U_{A11}	max. 4 A
Current consumption at U_{A11}	typ. 3 mA
	max. 2 A
Voltage supply U_{A12}	24 V DC
Power supply at U_{A12}	max. 4 A
Current consumption at U_{A12}	typ. 3 mA
	max. 4 A

Digital inputs

Input name	Digital inputs
Connection method	M12 connector
	2, 3, 4-wire

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Technical data

Digital inputs

Number of inputs	8
Protective circuit	Protection against polarity reversal
Filter time	3 ms
Input characteristic curve	IEC 61131-2 type 1
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	13 V DC ... 30 V DC

Digital outputs

Output name	Digital outputs
Connection method	M12 connector
	2, 3-wire
Number of outputs	8
Protective circuit	Short-circuit protection
Output voltage	24 V DC
Maximum output current per channel	500 mA

Classifications

eCl@ss

eCl@ss 4.0	27250302
eCl@ss 4.1	27250302
eCl@ss 5.0	27250302
eCl@ss 5.1	27242604
eCl@ss 6.0	27242604
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604

ETIM

ETIM 2.0	EC001430
ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized


Ex Approvals


UL Recognized / cUL Recognized / cULus Recognized

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

cULus Recognized 

Accessories

Accessories

Circular connector (cable-side)

Bus system connector - SACC-M12MSB-5CON-PG9 SH AU - 1507764



Bus system plug-in plug, male straight, 5-pos., M12, shielded, gold-plated contacts, B-coded, screw connection, metal knurl, cable screw connection Pg9

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Bus system connector - SACC-M12FSB-5CON-PG9 SH AU - 1507777



Bus system connector, female, straight, 5-pos., M12, shielded, gold-plated contacts, B-coded, screw connection, metal knurl, cable screw connection Pg9

Connector - SACC-M12MSB-5SC SH - 1513570



Connector, 5-position, shielded, Plug straight M12, B-coded, Spring-cage connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

Connector - SACC-M12FSB-5SC SH - 1513596



Connector, 5-position, shielded, Socket straight M12, B-coded, Spring-cage connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

Connector - SACC-M12MRB-5SC SH - 1513583



Connector, 5-position, shielded, Plug angled M12, B-coded, Spring-cage connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

Connector - SACC-M12FRB-5SC SH - 1513606



Connector, 5-position, shielded, Socket angled M12, B-coded, Spring-cage connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Connector - SACC-M12MS-5SC M - 1508187



Connector, 5-position, Plug straight M12, A-coded, Spring-cage connection, Knurl material: Zinc die-cast, nickel-plated, External cable diameter 4 mm ... 8 mm

Connector - SACC-M12FS-5SC M - 1508200



Connector, 5-position, Socket straight M12, A-coded, Spring-cage connection, Knurl material: Zinc die-cast, nickel-plated, External cable diameter 4 mm ... 8 mm

Data cable preassembled

Bus system cable - SAC-5P-M12MSB/ 2,0-900 - 1507065



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Free cable end, Cable length: 2 m

Bus system cable - SAC-5P-M12MSB/ 5,0-900 - 1507078



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Free cable end, Cable length: 5 m

Bus system cable - SAC-5P-M12MSB/10,0-900 - 1507081



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Free cable end, Cable length: 10 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Bus system cable - SAC-5P-M12MSB/15,0-900 - 1507094



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Free cable end, Cable length: 15 m

Bus system cable - SAC-5P- 2,0-900/M12FSB - 1507117



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Free cable end, on Socket straight M12, B-coded, Cable length: 2 m

Bus system cable - SAC-5P- 5,0-900/M12FSB - 1507120



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Free cable end, on Socket straight M12, B-coded, Cable length: 5 m

Bus system cable - SAC-5P-10,0-900/M12FSB - 1507133



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Free cable end, on Socket straight M12, B-coded, Cable length: 10 m

Bus system cable - SAC-5P-15,0-900/M12FSB - 1507146



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Free cable end, on Socket straight M12, B-coded, Cable length: 15 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Bus system cable - SAC-5P-M12MSB/ 0,3-900/M12FSB - 1507162



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 0.3 m

Bus system cable - SAC-5P-M12MSB/ 0,5-900/M12FSB - 1507175



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 0.5 m

Bus system cable - SAC-5P-M12MSB/ 1,0-900/M12FSB - 1507188



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 1 m

Bus system cable - SAC-5P-M12MSB/ 2,0-900/M12FSB - 1507191



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 2 m

Bus system cable - SAC-5P-M12MSB/ 5,0-900/M12FSB - 1507201



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 5 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Bus system cable - SAC-5P-M12MSB/10,0-900/M12FSB - 1507214



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 10 m

Bus system cable - SAC-5P-M12MSB/15,0-900/M12FSB - 1507227



Bus system cable, INTERBUS (500 kbps), 5-position, PUR halogen-free, Green RAL 6017, shielded, Plug straight M12, B-coded, on Socket straight M12, B-coded, Cable length: 15 m

Sensor/actuator cable

Sensor/Actuator cable - SAC-5P-MS/ 2,0-186 SCO - 1518326



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Free cable end, Cable length: 2 m

Sensor/Actuator cable - SAC-5P-MS/ 5,0-186 SCO - 1518339



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Free cable end, Cable length: 5 m

Sensor/Actuator cable - SAC-5P-MS/10,0-186 SCO - 1518342



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Free cable end, Cable length: 10 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Sensor/Actuator cable - SAC-5P-MS/15,0-186 SCO - 1518355



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Free cable end, Cable length: 15 m

Sensor/Actuator cable - SAC-5P- 2,0-186/FS SCO - 1518368



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Free cable end, on Socket straight M12 SPEEDCON, A-coded, Cable length: 2 m

Sensor/Actuator cable - SAC-5P- 5,0-186/FS SCO - 1518371



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Free cable end, on Socket straight M12 SPEEDCON, A-coded, Cable length: 5 m

Sensor/Actuator cable - SAC-5P-10,0-186/FS SCO - 1518384



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Free cable end, on Socket straight M12 SPEEDCON, A-coded, Cable length: 10 m

Sensor/Actuator cable - SAC-5P-15,0-186/FS SCO - 1518397



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Free cable end, on Socket straight M12 SPEEDCON, A-coded, Cable length: 15 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Sensor/Actuator cable - SAC-5P-MS/ 0,3-186/FS SCO - 1518407



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 0.3 m

Sensor/Actuator cable - SAC-5P-MS/ 0,5-186/FS SCO - 1518410



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 0.5 m

Sensor/Actuator cable - SAC-5P-MS/ 1,0-186/FS SCO - 1518423



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 1 m

Sensor/Actuator cable - SAC-5P-MS/ 2,0-186/FS SCO - 1518436



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 2 m

Sensor/Actuator cable - SAC-5P-MS/ 5,0-186/FS SCO - 1518449



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 5 m

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Sensor/Actuator cable - SAC-5P-MS/10,0-186/FS SCO - 1518452



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 10 m

Sensor/Actuator cable - SAC-5P-MS/15,0-186/FS SCO - 1518465



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 15 m

Sensor/Actuator cable - SAC-5P-MS/ 0,13-186/FS SCO - 1518481



Sensor/Actuator cable, 5-position, PUR, Black-gray RAL 7021, Plug straight M12 SPEEDCON, A-coded, on Socket straight M12 SPEEDCON, A-coded, Cable length: 0.13 m

Sensor/Actuator cable - SAC-5P-MSB/0,13-PUR/FSB SCO SH - 1518478



Sensor/Actuator cable, 5-position, PUR halogen-free, Black-gray RAL 7021, shielded, Plug straight M12 SPEEDCON, B-coded, on Socket straight M12 SPEEDCON, B-coded, Cable length: 0.13 m

Terminal marking

Zack Marker strip, flat - ZBF 12:UNBEDRUCKT - 0809735



Zack Marker strip, flat, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into flat marker groove, For terminal block width: 12 mm, Lettering field: 5.15 x 12.15 mm

Y-distributor

Distributed I/O device - FLM DIO 8/8 M12 - 2736848

Accessories

Y distributor - SAC-3P-M12Y/2XM12FS PE - 1683455



Y-distributor, 3-pos. +PE, straight plug M12 on 2 x straight socket M12

Phoenix Contact 2014 © - all rights reserved
<http://www.phoenixcontact.com>