

Decorative Vintage Candle

Decorative Vintage Candle 40W 230/240V E14 SV1

0023877



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Coloured
Lamp shape	Candle
Colour temperature (K)	2100
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288238777
Energy class	E
Cap/Base	E14
Watt (Nominal) (W)	40
Ordering number	0023877
Average life (Rated) (h)	2000
Luminous flux (Rated) (lm)	200
Technology	Incandescent
Voltage (V)	230-240

DATA TABLE

General data

Average life (Nominal) (h)	2000
Control gear required	No
Lamp finish	Coloured
Lamp shape	Candle
Dimmable	Yes
EAN code	5410288238777
Energy class	E
Energy saving lamp	No
General application	Hospitality
Intended purpose	Decor Lighting
Cap/Base	E14
Lamp mercury content (mg)	0

Decorative Vintage Candle

Decorative Vintage Candle 40W 230/240V E14 SV1

0023877

Ordering number	0023877
Product name	Decorative Vintage Candle 40W 230/240V E14 SV1
Average life (Rated) (h)	2000
Special purpose lamp	Yes
Starting time (max) (s)	0.01
Technology	Incandescent
Transformer required	No
Warm-up time to 60% of full light (max) (s)	Instant full light

Optical data

Colour temperature (K)	2100
CRI (Ra)	100
Luminous flux (Nominal) (lm)	200
Luminous flux (Rated) (lm)	200
Suitable for accent lighting	No

Electrical data

kWh per 1000 hours burning time	40
Lamp power factor	1
Watt (Nominal) (W)	40
Watt (Rated) (W)	40
Voltage (V)	230-240

Physical data

Max. Lamp Diameter (mm) - D	35
Lamp Length (mm) - C/L	98

Decorative Vintage Candle

Decorative Vintage Candle 40W 230/240V E14 SV1

0023877

