

Datasheet

Single H05Z-K Core Equipment Wire

7637570
7637573
7637577
7637583
7637586
7637589
7637592
7637595
7637599
7637602
7637606
7637609
7637612
7637615
7637618
7637621
7637628
7637630
7637637
7637640
7637643
7637646



A harmonised, halogen free wire, suitable for use in equipment in areas where toxic fumes and smoke may threaten life or equipment.

- **Conductor:** BS EN 60228 Class 5 flexible
- **Insulation:** Cross-linked low smoke and halogen free – Type EI5, Oxygen Index 30
- **Standards:** BS EN 50525-3-41, H05Z-K, Cenelec HD22.9
- **Approvals:** BASEC certified (except 0.5mm²)
- **Voltage Rating:** 2491B (H05Z-K) 0.5sqmm to 1.0sqmm - 300/500V
- **Temperature Range:** 0-90°C
- **Minimum Bend Radius:** 3 x overall diameter

Single H05Z-K Core Equipment Wire



Area (mm ²)	Construction	Insulation Thickness (mm)	Overall Diameter (mm)	Conductor Resistance @ 20°C (Ω/km Max)	Insulation Resistance @ 90°C (Ω/km Max)	Nominal Weight (kg/km)
0.5	16/0.2mm ²	0.6	2.18	39	0.0130	9
0.75	24/0.2mm ²	0.6	2.34	26	0.0110	13
1	32/0.2mm ²	0.6	2.52	19.50	0.0100	16
1.5	30/0.25mm ²	0.7	3	13.30	0.0100	21
2.5	50/0.25mm ²	0.8	3.25	7.98	0.0090	33
4	56/0.3mm ²	0.8	4.12	4.95	0.0070	47
6	84/0.3mm ²	0.8	4.9	3.30	0.0060	66
10	80/0.4mm ²	1.0	6.05	1.91	0.0056	111