





[www.cif.fr](http://www.cif.fr)

**Carbide tungsten drill**  
**Set of 10 bits**  
**Diameter 0.6 mm**  
**DU66.10**

---

This document contains manufacturer's information, protected through copyright. All rights reserved. This document can not be copied, reproduced or translated without written agreement from **C.I.F**

Information contained in this document can be modified without any prior notice

**CHARACTERISTICS****Carbure tungsten drill bit**

- Monopiece. Queue reinforced 3,17
- Diameter : 0.6 mm
- Minimum drilling speed 20 000 tr/min
- Most little is the diameter, higher will be the speed
- Descent speed from 1,6 to 4 m/min
- Option, drill bits with ring

**UTILISATION**

General use for drilling on different type of PCB support such as epoxy (typical use), EMC-1, EMC-3, etc..

[cif@cif.fr](mailto:cif@cif.fr)