

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	EBD0-0141-04	15MAR04	AM	FWK

NOTES

1. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
2. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
3. RATING

2.1 RATING : 3 AMPS

2.2 OPERATING TEMPERATURE : - 40°C TO +105°C
4. ELECTRICAL SPECIFICATION

3.1 INSULATION RESISTANCE
5000 MΩ MINIMUM

3.2 WITHSTAND VOLTAGE
500V AC
5. MATERIALS

4.1 CONTACT - BRASS, POST PLATE
Au 0.25µm (10µinch) IN CONTACT AREA
Sn 2 TO 3µm (80 TO 120µinch) IN SOLDER AREA.

4.2 HOUSING - BLACK POLYESTER UL 94V-0



- 6


NUMBER OF CONTACT POSITIONS TO BE INDICATED IN AREA SHOWN.
XX = NUMBER OF POSITONS.
- 7

TYCO LOGO TO BE PRESENT IN AREA INDICATED.

78.74	88.93	64	6-1634688-4
73.66	83.85	60	6-1634688-0
60.96	71.15	50	5-1634688-0
48.26	58.45	40	4-1634688-0
40.64	50.83	34	3-1634688-4
30.48	40.67	26	2-1634688-6
22.86	33.05	20	2-1634688-0
17.78	27.97	16	1-1634688-6
15.24	25.43	14	1-1634688-4
10.16	20.35	10	1-1634688-0
A	B	No Of Contacts	TYCO Part No
Dimensions			

Recommended P.C.Board
Hole Layout



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.MOREY 14JAN04		tyco Electronics Tyco Electronics Corporation Bideford, UK, EX39 4HE					
DIMENSIONS: MM		CHK J.SANDWELL 14JAN04							
		APVD F.WHEELER-KING 14JAN04		NAME BOX HEADER STRAIGHT					
		PRODUCT SPEC —							
		APPLICATION SPEC —							
		WEIGHT —							
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1634688	RESTRICTED TO —		
CUSTOMER DRAWING						SCALE NTS	SHEET 1	OF 1	REV B