





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-		P	REVISED PER ECO-11-005140	09APR2011	RK	HMR



DETAIL A
SCALE 5:1

1. 一般公差 : ± 0.3
 GENERAL TOLERANCE : ± 0.3
 材料 ソケットインシュレータ: PPS樹脂 色調: 黒
 ファイナルロック: 熱可塑性ポリエステル樹脂 色調: 白
 イニシャルロック: 熱可塑性ポリエステル樹脂 色調: 黒
 ロッキング&/バックプレート: 熱可塑性ポリエステル樹脂 色調: 黒
 プッシング: シリコンゴム 色調 1473712-1 : 赤茶
 1473712-2 : 緑
 シールリング: シリコンゴム 色調: 赤茶

SOCKET INSULATOR:PPS PLASTIC ,COLOR:BLACK
 FINAL LOCK:THERMOPLASTIC POLYESTER ,COLOR:WHITE
 INITIAL LOCK:THERMOPLASTIC POLYESTER ,COLOR:BLACK
 LOCKING & BACKPLATE:THERMOPLASTIC POLYESTER,COLOR:BLACK
 BUSHING:SILICONE RUBBER ,COLOR 1473712-1:RED BROWN
 1473712-2:GREEN


③ 適用電線サイズ SEAL RING: SILICONE RUBBER, COLOR: RED BROWN
APPLICABLE WIRE SIZE

型番 PART NO.	被 服 径 INSULATION DIA.	適 用 例 WIRE EXAMPLE
1473712-1	$\phi 1.6 \sim \phi 2.2$	AVSS 0.5 ~ 1.25 AESSX 0.5f ~ 1.25f
1473712-2	$\phi 2.0 \sim \phi 2.4$	AVX0.5f, AVX0.75f AESSX1.25f, AVSS1.25

4. 嵌合相手型番: 6473711-1, 6473711-2, 1473711-1, 1473711-2
PART NUMBER OF CAP ASSEMBLY TO BE MATED:
6473711-1, 6473711-2, 1473711-1, 1473711-2

1473712-2	
1473712-1	
PART NO.	NOTE

WIRE RANGE 捆合電線斷面積		INSULATION DIA 被覆外徑	
-----------------------	---	------------------------	---



NAME
名称 SUPER SEAL CONNECTOR
PLUG HOUSING 26POS. 2ROW ASSEMBLY

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A2	00779	C-1473712	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HIRANUMA	21AUG02
		CHK K. ODA	21AUG02
		APVD K. ODA	21AUG02
DIMENSIONS: 単位: 概 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.3	
		0 P-LC $\pm$ 1 P-LC ± 0.1 2 P-LC ± 0.03 3 P-LC ± 0.010 4 P-LC $\pm$	
MATERIAL 材料 		ANGLES 仕上 $\pm 1^{\circ}00'$	
		PRODUCT SPEC 製品規格 108-5824	
		APPLICATION SPEC 取付用規格 114-78011 114-78013	
		WEIGHT	28.2g
CUSTOMER DRAWING			