



LV HRC FUSE LINK GL/GG WITH INSULATED GRIP LUGS WITH COMBINATION INDICATOR SIZE 00, 160A, AC 500V/DC 250V

Similar to image

Technical data:

Current / for AC / rated value	A	160
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH00
Supply voltage		
• for AC / rated value	V	500
• for DC	V	250
Switching capacity current		
• in accordance with IEC 60947-2 / rated value	kA	120
• with DC / in accordance with IEC 60947-2 / rated value	kA	25
Design of an identification indicator		Combination alarms
Ambient temperature		
• minimum	°C	-5
• maximum	°C	40

Certificates/approvals:

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
 KEMA ROSTEST	 VDE Manufacturer	Manufacturer	 GL

Further information:



Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/lowvoltage/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3NA6836/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA6836

CAX-Online-Generator
<http://www.siemens.com/cax>



last change:

Aug 26, 2011