

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISED			
P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-	H3	REVISED	ECR-08-031766	10DEC08 SF KB

Dimensions: 18.6^{+0.5}, ±0.3, 7, ±0.3, 3.5, 2-∅2.4, (89.1), -AMP, -A-

Dimensions: 15.8^{+0.5}, 12.8, 5.9, 3.15, (7.35), 2.35, 0, 3.5, 7, 12.5, 16, 21.5, 25, 2.35, 0, 3.5, 7, 10.5, 12.5, 16, 19.5, 23, 25, 28.5, 32, 35.5, 82.5, (75.5), 29.7, 40.2

PC BOARDED DIMENSION
 プリント基板取付穴

NOTE (注記);
 1. THICKNESS (板厚); 1.6±0.15
 2. TOLERANCE (公差); ±0.1

Dimensions: 2-∅3.2, 7.35, 0, 3.5, 7, 12.5, 16, 21.5, 25, 32.3, 35.8, 39.3, 42.8, 44.8, 48.3, 51.8, 55.3, 57.3, 60.8, 64.3, 67.8, 30-∅1, 4.6, 5, 15 MAX. (最大), 82.5

△ [-Z-] 面より2mmの範囲で測定。
 △ 相手ハウジングと所定の機能を満足して嵌合できること
 3. プリント基板への取付は、JIS B1115又は1122 M3×6ナベ (2種又は4種) のタッピンネジで締付けた後ハンダ付する (締付けトルク: 0.4N-m 以下)
 △ 回路番号: 下図参照のこと。

△ TO BE MEASURED BETWEEN [-Z-] AND 2
 △ TO BE MATE WITH PLUG HSG SMOOTHLY
 3. TO BE USE M3 TAPPING SCREW JIS B1115 OR 1122 (TYPE 2 OR 4) BEFORE SOLDER
 △ CIRCUIT NUMBER.

13121110, 9876, 54, 321, 302928, 27262524, 232221, 2019, 1817, 161514

Dimensions: 0.64 THK(板厚), 4.6, (5), 4±0.4

TOLERANCE UNLESS OTHERWISE SPECIFIED:
 一般公差
 0 < x ≤ 10 : ±0.2
 10 < x ≤ 30 : ±0.25
 30 < x ≤ 100 : ±0.3
 ANGLE : ±3°
 角度

HB	1~30 (全極)	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD	WHITE	2-5173866-1
	1~30 (全極)	TIN-LEAD	SELECTIVE GOLD	GREEN	2-173866-4
SEE 4-173866-2					4-173866-2
SEE 4-173866-1					4-173866-1
V-2		PRE-TIN		WHITE	9-173866-1
HB	1~30 (全極)	TIN-LEAD	SELECTIVE GOLD	WHITE	2-173866-1
		PRE-TIN		GRAY	173866-6
		PRE-TIN		GREEN	173866-4
		PRE-TIN		WHITE	173866-1
FLAMMABILITY OF MATERIAL 使用材料難燃グレード	金めっきタブ回路NO. SELECTIVE GOLD CIRCUIT NO. △	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	色 COLOR	型番 PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 19SEP03	Tyco Electronics Corporation Kawasaki, Japan		
DIMENSIONS: 単位: 桁 mm		CHK K.BETSUI 19SEP03	NAME 070 SERIES MULTI-LOCK I/O CONNECTOR 30POSITION CAP HOUSING ASSEMBLY		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.BETSUI 19SEP03	DRAWING NO 173866		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 108-5216	RESTRICTED TO		
MATERIAL 材料 HOUSING: PBT CONTACT: BRASS		FINISH 仕上 SEE TABLE	WEIGHT 16.4g	SIZE A2	CAGE CODE 00779
			SCALE 2:1	SHEET 1 of 1	REV H3

AMP 1471-9 REV 31MAR2000

173866

A