



ENGLISH

Datasheet

Stock No: 137-1230

RS Pro Natural Nylon Cable Tie, 775mm x 8.9 mm, SL



Image representative of range

Product Details

Cable ties, type SES-QUICK

Transparent polyamide 6.6.

Cable Ties - Nylon



ENGLISH

Specifications

Length	775mm
Width	8.9 mm
Colour	Natural
Material	Nylon 66
Quantity	100
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+85°C
Series	SL
Tensile Strength	790N
Maximum Bundle Diameter	230mm