

T-Series in PA66 black, Article number: 111-01980



[6 more images to T18R >](#)



Features

- Available in a wide range of materials and sizes
- High tensile strength with very low insertion force
- Only high quality plastic is used meeting recycling targets
- Inside serrated cable ties for a strong hold onto bundles
- Ergonomic bent tail offers quick and simple installation
- Easy application either manually or with an application tool

Certifications & Approvals



Application

T-Series cable ties for bundling and securing of cables, pipes and hoses. These cable ties can be used for nearly all kind of applications.

T-Series in PA66 black is suitable for following markets and industries



More products in this product group

[Cable Ties Polyamide 6.6 standard >](#)

Base Data

Application Tool	MK3PNSP2, MK3SP, MK20, EVO7
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	Cable Tie 100x2.5 black
Fixation Method	None
GLOBAL PART NAME	T18R-PA66-BK
Identification Plate Position	none
Pack Cont.	1000
Package Quantity per	pieces
Product Family	T-Series in PA66 black
Product Group	Cable Ties Polyamide 6.6 standard
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated

Product Dimensions



Bundle Ø max.	22.0 mm
Bundle Ø min.	1.5 mm
Length (L)	100.0 mm
Min.Tensile Strength	80 N
Thickness (T)	1.0 mm
Width (W)	2.5 mm

Material and Specifications

ELV compliant (Article 4 - 2)	YES
Flammability	UL 94 V2
Halogenfree	Yes
Hazardous goods	No
Material	Polyamide 6.6 (PA66)
Operating Temperature - °C	-40 °C to +85 °C, (+105 °C, 500 h)
Specifications	