



mecalectro

Small linear solenoid for intensive use – 8.54.AA.62



Stroke: 4 mm

Force at beginning of stroke (FM: 100/25/5%):
0.5/1.5/5.6 N

Force at end of stroke (FM: 100/25/5%):
2.4/4.9/12 N

Power Consumption (FM: 100/25/5%):
5.3/16/60 W

Total mass: 45 g

Degree of protection / Energetic class: IP 40 / B
Standard supplies: 24Vcc

Possible supplies: From 6 to 125Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automaton, electrical equipment, machinery, security applications.