

Product selector

M8 Pico DC cordsets

Type	Face View	Cable Length	Part No.	List price USD
ecolink M8 Pico DC cordsets • 3-wire • PUR jacket				
	Female 	Pin 1 brown Pin 3 blue Pin 4 black 2 m	EVC 141	\$11.95
		5 m	EVC 142	\$14.95
		10 m	EVC 143	\$20.50
	Female 	Pin 1 brown Pin 3 blue Pin 4 black 2 m	EVC 144	\$11.95
		5 m	EVC 145	\$14.95
		10 m	EVC 146	\$20.50
	Female 	Pin 1 brown Pin 3 blue Pin 4 black 2 m, 2 LED	EVC 147	\$15.50
		5 m, 2 LED	EVC 148	\$18.50
		10 m, 2 LED	EVC 149	\$23.50

ecolink M8 Pico DC cordsets • 4-wire • PUR jacket

	Female 	Pin 1 brown Pin 2 white Pin 3 blue Pin 4 black 2 m	EVC 150	\$12.95
		5 m	EVC 151	\$15.95
		10 m	EVC 152	\$21.50
	Female 	Pin 1 brown Pin 2 white Pin 3 blue Pin 4 black 2 m	EVC 153	\$12.95
		5 m	EVC 154	\$15.95
		10 m	EVC 155	\$21.50

Technical Specs – Cordsets

Operating voltage:	Without LED: 50 V AC / 60 V DC With PNP LED: 10...36 V DC
Current rating:	3 A
Protection rating:	IP67 / IP68 / IP69K
Tightening torque:	0.3...0.5 Nm
Ambient temperature:	-25...90 °C
Flex rating:	> 5 million cycles
Material body:	TPU housing, Viton O-ring
Material coupling nut:	Nickel-plated brass
Cable:	PUR, halogen-free, 24 AWG conductors, Ø 3.7 mm
Approvals	cURus

Technical Specs – Field Wirable Connectors

Operating voltage:	60 V AC / 75 V DC
Protection rating:	IP67
Ambient temperature:	-25...90 °C
Material body:	Nickel-plated brass (L33600, L33601, E18216, E18218) PA (L33602, L33603, E18217, E18219)
Material coupling nut:	Nickel-plated brass

M8 Pico DC field wirable connectors

Type	Face View	Cable Diameter	Part No.	List price USD
------	-----------	----------------	----------	----------------

3-pin M8 Pico DC field wirable connectors • Solder termination

	Male 	3.5...5.0 mm range	L 33600	\$14.50
	Female 	3.5...5.0 mm range	L 33602	\$14.50

4-pin M8 Pico DC field wirable connectors • Solder termination

	Male 	3.5...5.0 mm range	L 33601	\$15.50
	Female 	3.5...5.0 mm range	L 33603	\$15.50

3-pin M8 Pico DC field wirable connectors • Insulation displacement

	Male 	3...5 mm range	E 11550	\$16.50
	Female 	3...5 mm range	E 11552	\$16.50

4-pin M8 Pico DC field wirable connectors • Insulation displacement

	Male 	3...5 mm range	E 11551	\$17.50
	Female 	3...5 mm range	E 11553	\$17.50



PRODUCT TIP

Have an application that requires an exact patchcord length?

In less than two minutes, you can convert a cordset into a patchcord by attaching a field wirable connector. Wirable connectors give you flexibility to extend or shorten the cable length according to your application.

And, if you have long bulk sections of cable, field wirable connectors allow you to make your own cordsets.

DC

M8 cordsets Automation/Oils	M8 wiring blocks Automation/Oils	M12 cordsets Automation/Oils	M12 wiring blocks Automation/Oils	M12 cordsets Washdown	M12 cordsets Welding	M12 cordsets Hazardous/Mobile	M12 DIN-style Automation	M12~20UNF cordsets Automation/Washdown
								
4 • 5	6 • 7	8 • 11	12 • 13	14 • 15	16 • 17	18 • 19	20 • 21	22 • 23

AC