



ENGLISH

Datasheet

PVC 10m Long White Flexible Tube Reinforced, 40mm Bend Radius

RS Stock number 197-8229

KEY FEATURES:

- | Aquavend will not support microbiological growth.
- | WRAS approved construction. Certification available on request or downloadable from www.copely.com
- | Cadmium and silicone-free.
- | Manufactured using Copely's unique ultra-hygienic heat bonding technology eradicating the need for chemicals.
- | High quality PVC outer extruded with a brilliant white 'clinical' finish.
- | TPE mirror smooth inner for improved flow.
- | Odourless and taint free specialist materials.
- | Good flexibility and durability.
- | Excellent resistance to abrasion.
- | Specially selected high tensile polyester fibres used at the optimum braid angle of 54° 44'(54.73°) creates an effectively balanced pressure hose.
- | Good kink resistance across a wide temperature range.
- | Independently tested in accordance with BS 6920.



SIZES:

- | Available in 30m coils
- | 6.3mm-25mm ID

COLOURS:

- | Black liner / White outer
- | Custom sizes and colours available on request subject to minimum order quantity.

APPLICATION EXAMPLES:

- | Vending Machines.
- | Water Softeners.
- | Drinking Water.
- | Popular with the caravan and marine industry for water supply tubing.



ENGLISH

Product Ref		PHR06	PHR10	PHR12	PHR19	PHR25
Ex Stock	30m roll	●	●	●	●	●
Nominal size		6.3 x 12mm	10 x 16mm	12.5 x 19mm	19 x 26mm	25 x 33mm
Internal Diameter		6.3 ± 0.25mm	10.0 ± 0.25mm	12.5 ± 0.25mm	19.0 ± 0.25mm	25.0 ± 0.25mm
External Diameter		12.0 ± 0.30mm	16.0 ± 0.30mm	19.0 ± 0.30mm	26.0 ± 0.30mm	33.0 ± 0.50mm
Length Tolerance		BS EN ISO 1307 (± 1%)				
Maximum Working Pressure		10 Bar	10 Bar	10 Bar	10 Bar	10 Bar
Minimum Burst Pressure		80 Bar	60 Bar	44 Bar	40 Bar	30 Bar
Bend radius		30mm	40mm	55mm	135mm	210mm
Working Temperature		- 15°C to + 70°C				
Material		Hytrel / Flexible PVC				
Material Softness		BSS45 FDA Approved				
Flammability		Self Extinguishing				
Weight per meter		0.110Kg	0.158Kg	0.207Kg	0.300Kg	0.500Kg
Coil Weight		3.30Kg	4.73Kg	6.20Kg	9.00Kg	15.00Kg
Packaging		Strapex Ties and Shrinkwrap				
Applicable Standards		WRAS Aproved Registration Number 1004503				