
Xpelair GX6



Maximum air flow	Metres ³ per second	266
Maximum air flow	Litres per second	74
Sound pressure level	dB(a)@3m	37
Electrical power rating	Watts	30
IP rating		IP25
Weight	Kilograms	1.9
Guarantee	Years	2