

## Datasheet

# RS Pro Toggle Switch SPDT On-Off-On, 1.5 A@ 250 V ac, 3 A@ 28 V dc, 3 A@125 V ac, Panel Mount

RS Stock No: **448-1071**



## Product Details

RS Pro SPDT toggle switch has epoxy sealed terminals to prevent contamination during soldering. This panel mount switch performs on-on operation. It withstands currents up to 3 A at 28 V dc voltage. The silver plated coin silver contacts offer superior performance.

## Features and Benefits

- Silver contacts
- Solder termination method
- Terminals epoxy sealed against flux and dirt
- Brass actuator and diallyl phthalate case

**Specifications:**

Actuator Length	9.4 mm
Actuator Material	Chrome Plated Brass
Contact Configuration	SPDT
Contact Current Rating	3 A at 125 V ac or 28 V dc, 1.5 A at 250 V ac
Contact Material	Silver Plated Coin Silver
Contact Resistance	20 mΩ
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-30°C
Mounting Type	Panel Mount
Operating Temperature Range	-30 to +85°C
Standards Met	UL Approved
Switch Operation	On-Off- (On)
Terminal Type	Solder