



ENGLISH

## Datasheet

Stock No: 180-7127

# RS Pro Conductivity Meter, 0.1 → 199.9 $\mu\text{S}/\text{cm}$ , 0.2 → 19.99 $\text{mS}/\text{cm}$



Range	Resolution	Accuracy
Temperature		
0 → +60 °C	±0.1°C	±0.8°C
+32 → +140 °F	±0.1°F	±1.5°F

## Product Details

### Conductivity Meter with RS-232 Serial Link

This instrument has a detachable carbon rod electrode and measures conductivity and temperature.

- Auto power down
- Display hold function
- Large dual LCD display with contrast adjustment
- Records maximum, minimum and average readings
- Requires a PP3 battery, not supplied



ENGLISH

## Specifications:

Maximum Conductivity	19.99 mS/cm, 199.9 $\mu$ S/cm
Minimum Conductivity	0.1 $\mu$ S/cm, 0.2 mS/cm
Best Accuracy	$\pm 2\%$ + 1 Digit
Resolution	0.01 mS/cm, 0.1 $\mu$ S/cm
Battery Type	9V
Power Source	Battery
Dimensions	180 x 72 x 32mm
Height	32mm
Length	180mm
Width	72mm
Model Number p	CD-4303