

HBL2721 -- Twist-Lock Plug



3P4W, 30A 3PH 250V, L15-30P, Black & White Nylon

Product Specifications

Product Type



Product Item	Plug
Wiring Scheme	3-Pole, 4-Wire Grounding
Amperage	30A
Voltage	3 Phase 250V AC
NEMA Configuration	L15-30P
Item Style	Insulgrip
Device Color	Black/White
Horsepower	3
Cord Dia.	.35"-1.15" (9-29)
Blade Holder Material	Natural White Nylon
Terminal Retainer Material	Clear polycarbonate
Housing Material	Black nylon
Cord Clamp Material	Natural (white) nylon
Blade Material	Brass
Terminal Clamp Material	.08" (2) steel-nickel plated
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive
Ground Screw Material	#10-32 Brass (green finish) Multi-drive
Cord Clamp Screw Material	Steel, zinc plated Multi-drive
Body Holding Screw Material	Steel, zinc plated Multi-drive
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a

Temperature Rise	power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	30A #10 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	FED SPEC UL/CSA
UPC Number	783585039220
Weight in LBs	0.25
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

