

Product Information

ETX085x75-Ø20 NL80-Type E

EAN 4031582332032

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	75 mm
Axle Hole Ø	20 mm
Hub length	80 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	800 kg
Static Load capacity	1600 kg
Hardness of tread	A 92 Shore

