

Datasheet

RS Pro AC Axial Fan, 119.5 x 119.5 x 38.5mm, 187m³/h, 15W, 230 V ac (OA109 Series)

RS Stock No: **789-7902**



Product Details

RS Pro AC axial fan measures 119.5 x 119.5 x 38.5 mm. It has a power rating of 15 W and voltage rating of 230 V ac. It features a cast aluminium frame, AC shaded pole and impedance protected motor. This dual ball bearing fan delivers a superior airflow of 187m³/h with a rotating speed of 3000 rpm. It is suitable for automotive, appliances, computer and IT, medical and laboratory, telecom and industrial control cabinets.

Features and Benefits

- Diecast aluminium frame
- 6000 hours life time
- Dual ball bearing
- UL, cUL, TUV approved

**Specifications:**

AC or DC Operation	AC
Air Flow	187 m ³ /h
Bearing Type	Ball
Configuration	Square
Depth	38.5 mm
Dimensions	119.5 x 119.5 x 38.5 mm
Direction of Curve	Forward
Fan Speed	3000 rpm
Height	119.5 mm
Noise Level	42 dB
Power Consumption	15 W
Special Features	AC Shaded Pole, Impedance Protected & Thermally Motor
Static Pressure	0.28 inH ₂ O
Supply Voltage	230 V ac
Termination Type	Lead Wire
Width	119.5 mm
Frame Material	Diecast Aluminium
Impeller Material	PBT
Insulation Resistance	>100 MΩ
Life Expectancy	60000 h
Standards Met	UL, cUL, TUV