



ES65A 110 Degrees Motion Sensor 150W UFO Floodlight

Features :

- 110 degrees PIR motion sensor with no dead-angle wide view design
- 150W lighting load capacity
- Manual override facility to set floodlight continuously on
- Automatic dusk-to-dawn control
- Suitable for indoor & outdoor installations

Specification

Voltage Requirement	AC220-240V / 50Hz
Lighting Load (Incandescent)	Max. 150W
Detection Range	Min. 12m, 110° (20°C)
Swiveling Angle	180° Vertical (Lamp Part) 30° Vertical, 330° Horizontal (Sensor Part)
Mounting Height	Recommended 1.8~2.0m (Wall Mount)
Wall Switch Control	On / Off / Manual Override
Time Adjustment	5 sec. ~ 12 min.
Lux Adjustment	0~1000 Lux Adjustable
Operating Temperature	-20°C~40°C
Warm Up Time	Approx. 1 min.
Protection Class	I
Protection Degree	IP44
Safety	CE, GS