

Specifications for BMP41/BMP51/BMP53 Labelmaker Tags

Article No.	143237
Brady Material No.	B-412
Material Type	Polypropylene Tag
Colour	Black on White
Finish	Matt
Order Reference	MC-625-412
Printer Compatibility	BMP41; BMP51; BMP53
Size - Length (m)	6.10
Size - Width (mm)	15.88
Additional Information	Non-Adhesive Slide-in Strips
Thickness (mm)	0.201
Total Qty per Pack	1 Insert(s) / Box
Application	Voice & Data Communication
Industry	Data & Telecommunications; Electrical
Layout	Continuous Roll
Description	These tags are designed to be printed, cut to length and act as a slide-in strip for voice/data punch blocks inserts & faceplate inserts. Offers high print legibility and high tensile strength.
Max. Service Temp. °C	100
Min. Service Temp. °C	-40
Shape	Continuous
Software	LabelMark
Voice/Data Application	1-4 Outlet Faceplates; 110 Blocks; BIX Blocks; Broadcast Patch Bay Strips; Desi-Strip Inserts; Non-Adhesive Slide-in Strips