

TLS PC Link™ Thermal Transfer Printer Specifications



- Weight 2.50 lbs. (1.14 kg)
- Thermal transfer print mechanism 203 dpi (8 dots/mm)
- Custom TrueType font
- Labels up to 2" wide (50.8 mm)
- Print width 1.81" (46 mm)
- Print length up to 6" (152.4 mm)
- Operating temperature range: 40° F to 120° F (4° C - 49° C)
- UL and CUL listed battery charger - 120v/60hz input 12VDC 300ma output
- FCC Class A approved
- Prints over 500 labels between battery charges
- Adjustable for 6 different widths of labels
- Built in industrial label cutter
- 6 month warranty

