


Socket - EM-DUO 120/20/GFI/AUX - 5603049

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Rail-mountable double socket



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 349031
Weight per Piece (excluding packing)	310.9 g
Custom tariff number	85366990
Country of origin	United States

Technical data

Dimensions

Width	83 mm
Height	134 mm
Depth	49 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Nominal voltage U_N	125 V AC
Nominal current I_N	20 A
For country-specific use in	USA
	Canada
	China
	Japan
	Mexico
	Peru
	Saudi Arabia

Socket - EM-DUO 120/20/GFI/AUX - 5603049

Technical data

General

	Taiwan
	Thailand
	Phillipines
	Venezuela
	Vietnam
Color	ivory
Insulating material	PVC 94 V0
Standards/regulations	UL 508
	CSA 22.2

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	30
Conductor cross section AWG/kcmil max	10
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143412
eCl@ss 5.1	27143412
eCl@ss 6.0	27143412
eCl@ss 7.0	27440519
eCl@ss 8.0	27440519

ETIM

ETIM 3.0	EC001325
ETIM 4.0	EC001663
ETIM 5.0	EC001663

UNSPSC

UNSPSC 6.01	30211806
UNSPSC 7.0901	39121406
UNSPSC 11	39121406
UNSPSC 12.01	39121406

Socket - EM-DUO 120/20/GFI/AUX - 5603049

Classifications

UNSPSC

UNSPSC 13.2	39121406
-------------	----------

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approvals submitted

Approval details

UL Listed	
mm ² /AWG/kcmil	30-10
Nominal current I _N	20 A
Nominal voltage U _N	125 V

cUL Listed	
mm ² /AWG/kcmil	30-10
Nominal current I _N	20 A
Nominal voltage U _N	125 V

cULus Listed	
--------------	--