

Screw connection - WP-G HF IP66 M10 BK - 3240895


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, metric thread, IP66 protection, straight



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710022
Weight per Piece (excluding packing)	3.96 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	34.5 mm
Width (a)	17 mm
Wrench size	16.00 mm
Outside diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

General

Color	black
Type	Straight
	Outer thread
Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	V0

Screw connection - WP-G HF IP66 M10 BK - 3240895

Technical data

General

Material	PA
----------	----

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / LR


Ex Approvals


Approvals submitted

Approval details

Screw connection - WP-G HF IP66 M10 BK - 3240895

Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 10,0 BK - 3240680



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 10,0 BK - 3240838



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m