



## Product Information

### ETX085x70-Ø20 NL75-Type A

EAN 4031582330861

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	70 mm
Axle Hole Ø	20 mm
Hub length	75 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	700 kg
Static Load capacity	1400 kg
Hardness of tread	A 92 Shore

