

4

3

2

1

REVISIONS			
EC	REV	DESCRIPTION	DATE
CPR	A1	REVISED PER ECO-11-005140	25MAR11

7. CONTACTS PURCHASED SEPARATELY.

6. ELCON EQUIVALENT SERIES 298-08-01100.

5. ITEMS PROVIDED TO THIS SPECIFICATION TO BE PERMANENTLY IDENTIFIED PER THE FOLLOWING IDENTIFIER:

TE CONNECTIVITY PART NUMBER

DATE CODE (e.g. 0601)

YEAR

WEEK

XXXXXXXX-X

XXXX

4

A REFERENCE DIMENSION (X.XX) IS WITHOUT TOLERANCE AND USED FOR INFORMATION ONLY.

3. FINISHES:

RETENTION CLIPS: BRITE DIP PICKLED PER INDUSTRY STANDARDS.

2. MATERIALS:

INSULATORS: THERMOPLASTIC, GLASS REINFORCED, UL94V-0 FLAMMABILITY RATED, COLOR-BLACK.

RETENTION CLIPS: COPPER OR STAINLESS STEEL.

1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TE CONNECTIVITY APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.

NOTES: UNLESS OTHERWISE SPECIFIED

INCH MM OR INCH (MM) THIRD ANGLE PROJECTION UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES (METRIC) TOLERANCES ANGLES ± .5° DECIMALS .XXX ± .010 (.25) .XX ± .02 (.3)	DRAWN R. F. A.	DATE 3/1/06	TE Connectivity ELCON TITLE CONNECTOR, SOCKET SIZE #12, #20, #12 CONFIG. LOWER DRAWER		
	CHECKED				
	APPROVED		SIZE DWG NUMBER REV. B C= 1648206 A1		
	APPROVED S. FLICKINGER	3/3/06			
	DCA APPROVED		ACAD FILE NUMBER C1648206A.DWG		
			DWG SCALE 1=1		SH 1 OF 2


4

3



2

1

REVISIONS			
EC	REV	DESCRIPTION	DATE
		SEE SHEET 1	



FRONT VIEW



REAR VIEW

INCH MM OR INCH (MM) THIRD ANGLE PROJECTION UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES (METRIC) TOLERANCES ANGLES ± .5° DECIMALS .XXX ± .010 (.25) .XX ± .02 (.3)	DRAWN R. F. A.	DATE 3/1/06	TE Connectivity	
	CHECKED		TITLE CONNECTOR, SOCKET SIZE #12, #20, #12 CONFIG. LOWER DRAWER	
	APPROVED			
	APPROVED S. FLIKINGER	3/3/06		
	DCA APPROVED		SIZE B	DWG NUMBER C= 1648206
ACAD FILE NUMBER		C1648206A.DWG		REV. A1
			DWG SCALE	1=1
			SH 2 OF 2	