


D

C

B

A



- 1 MATERIAL: HOUSING- POLYCARBONATE, CLEAR
TERMINAL- .36 [.014] THICK PHOSPHOR BRONZE PLATED
WITH .178 μ m [.000007] THICK GOLD IN LOCALIZED
PLATE AREA OVER .762 μ m [.000030] THICK PALLADIUM
NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m [.000100]
THICK NICKEL ON ENTIRE CONTACT.
2. PLUG WILL ACCEPT 0.89[.035] DIAMETER
STRANDED, 26 OR 28 AWG, OR TINSEL 28
AWG WIRE WITH A 4.58[.180] DIAMETER
MAXIMUM JACKET.
- 3 TERMINATED DIMENSION 6.15[.242]
MAXIMUM.
- 5 DIMENSIONS ARE MAXIMUM UNLESS
OTHERWISE SPECIFIED.
- 6 10,000 ASSEMBLIES PER PACKAGE.
- 7 1000 ASSEMBLIES PER PACKAGE.
- 8 100 ASSEMBLIES PER PACKAGE.

OBSOLETE	8	LOOSE PIECE	5-554710-3
	7		5-554710-2
	6		5-554710-1
		REELED	554710-1
	PACKAGED	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL CHK B. MCNEILL APVD B. MCNEILL		11DEC2007 11DEC2007 11DEC2007		 TE Connectivity	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MODULAR PLUG ASSEMBLY, 6 POSITION, ROUND CABLE -	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163 APPLICATION SPEC 114-6016		SIZE A2	
MATERIAL - 		FINISH - 		WEIGHT -		CAGE CODE 00779	
				CUSTOMER DRAWING		DRAWING NO C-554710	
						RESTRICTED TO -	
						SCALE 4:1	
						SHEET 1 of 1	
						REV P	