

Decorative Vintage A19

Decorative Vintage A19 60W 230/240V E27 SV1

0023869



Range Features

-

PRODUCT OVERVIEW

Lamp finish	Coloured
Lamp shape	GLS
Colour temperature (K)	2050
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288238692
Energy class	E
Cap/Base	E27
Watt (Nominal) (W)	60
Ordering number	0023869
Average life (Rated) (h)	2000
Luminous flux (Rated) (lm)	245
Technology	Incandescent
Voltage (V)	230-240

DATA TABLE

General data

Average life (Nominal) (h)	2000
Control gear required	No
Lamp finish	Coloured
Lamp shape	GLS
Dimmable	Yes
EAN code	5410288238692
Energy class	E
Energy saving lamp	No
General application	Hospitality
Intended purpose	Decor Lighting
Cap/Base	E27
Lamp mercury content (mg)	0

Decorative Vintage A19

Decorative Vintage A19 60W 230/240V E27 SV1

0023869

Ordering number	0023869
Product name	Decorative Vintage A19 60W 230/240V E27 SV1
Average life (Rated) (h)	2000
Special purpose lamp	Yes
Starting time (max) (s)	0.01
Technology	Incandescent
Transformer required	No
Warm-up time to 60% of full light (max) (s)	Instant full light

Optical data

Colour temperature (K)	2050
CRI (Ra)	100
Luminous flux (Nominal) (lm)	245
Luminous flux (Rated) (lm)	245
Suitable for accent lighting	No

Electrical data

kWh per 1000 hours burning time	60
Lamp power factor	1
Watt (Nominal) (W)	60
Watt (Rated) (W)	60
Voltage (V)	230-240

Physical data

Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	108

Decorative Vintage A19

Decorative Vintage A19 60W 230/240V E27 SV1

0023869

