

**SOLID P 191513 G**



Sample photo

**Order symbol:** P 191513 G  
**Product nbr:** 8855209  
**Description:** Enclosure, Polyester  
**Remarks:** Grey cover

**EAN:** 6418074064035  
**El. number:**  
Finland: 3438011  
Denmark: 8212040009  
Sweden: 8855209  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		185	150	130	Ingress Protection (EN 60529): IP 67
<b>inch:</b>		7.3	5.9	5.1	Impact Resistance (EN 62262): IK 10
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polyester			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7036			UV resistance: UL 508
<b>Cover colour:</b>		RAL 7036			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Cover screws material:</b>		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Cover screws colour:</b>		Black			NEMA Class: NEMA 3, 3R, 4, 4X, 6, 6P, 12, 13
<b>Gasket material:</b>		PUR			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-50 ... 160 °C			Gost R
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-58 ... 320 °F			
<b>Continuous:</b>		-40 ... 176 °F			
<b>Accessories:</b>					
MP 1915		Mounting plate			
MPX 1915		Mounting plate			
MPS S3		Mounting set for mounting plates			
DRF 321		DIN rail frame			

P191505 Top view -cover removed

