



### Technical specifications and standard

**European directive :**  
89/686/CEE

**Norms :**  
EN361

**EC type attestation :**  
0082/490/160/07/02/0237

**Quality Assurance**  
AFAQ: ISO 9001 : Version 2000

**Certification number :**  
0333 AFAQ/CTH

**Marking :**  
MILLER



[click address to go to....](#)

# DURAFLEX VEST HARNESS - SIZE M/L

## Product use

**High Visibility Vest Harness Miller DuraFlex 2 points, rear & front anchorage with Teflon finish. (front anchorage soft webbing loops)**

## Technical description

### Shoulders & legs straps

Duraflex stretchable 45 mm webbing  
Polyamide & elastomere  
Breaking strength: > 2200 daN

### D-ring (rear & belt):

Raw material: Ø7 mm stainless steel  
Breaking strength: > 5000 daN

### Quick buckles :

Raw material : stainless steel & aluminium  
Breaking strength : > 900 daN

### Adjustment buckles :

Raw material : 45 mm Aluminium alloy  
Breaking strength : > 850 daN

### Heavy duty vest multiples pockets :

Raw material : 80% polyester, 20% cotton

**Weight :** 1.400 kg

Tests : Static test : >15KN  
Temperature : -30°C à +50°C

## Additional information

# DURAFLEX VEST HARNESS - SIZE M/L

The supplier or its legal representative supplier settled in the European community :

**MILLER**

declares that the new Individual Protection Equipment described hereafter :

Designation :

**DuraFlex Vest Harness - Size M/L**

Article code :

**10 068 82**

is in conformity with Directive dispositions 89/686/CEE.

This PPE has been the object of the EC attestation type :

**0082/490/160/07/02/0237**

delivered by :

**APAVE Lyonnaise  
177 route de Saint-Bel  
69811  
TASSIN CEDEX  
France**

Identified by the number :

**0082**

Made on the : **05/08/2004**

at : **Vierzon**

Division : **Fall Protection**

By : **Frederic GUICHARD**

[click address to go to....](#)



### Technical specifications and standard

**European directive :**  
89/686/CEE

**Norms :**  
EN361

**EC type attestation :**  
0082/490/160/07/02/0237

**Quality Assurance**  
AFAQ: ISO 9001 : Version 2000

**Certification number :**  
0333 AFAQ/CTH

**Marking :**  
MILLER



[click address to go to....](#)

# DURAFLEX VEST HARNESS - SIZE XL

## Product use

**High Visibility Vest Harness Miller DuraFlex 2 points, rear & front anchorage with Teflon finish. (front anchorage soft webbing loops)**

## Technical description

### Shoulders & legs straps

Duraflex stretchable 45 mm webbing  
Polyamide & elastomere  
Breaking strength: > 2200 daN

### D-ring (rear & belt):

Raw material: Ø7 mm stainless steel  
Breaking strength: > 5000 daN

### Quick buckles :

Raw material : stainless steel & aluminium  
Breaking strength : > 900 daN

### Adjustment buckles :

Raw material : 45 mm Aluminium alloy  
Breaking strength : > 850 daN

### Heavy duty vest multiples pockets :

Raw material : 80% polyester, 20% cotton

**Weight :** 1.855 kg

Tests : Static test : >15KN  
Temperature : -30°C à +50°C

## Additional information

# DURAFLEX VEST HARNESS - SIZE XL

The supplier or its legal representative supplier settled in the European community :

**MILLER**

declares that the new Individual Protection Equipment described hereafter :

Designation :

**DuraFlex Vest Harness - Size XL**

Article code :

**10 075 50**

is in conformity with Directive dispositions 89/686/CEE.

This PPE has been the object of the EC attestation type :

**0082/490/160/07/02/0237**

delivered by :

**APAVE Lyonnaise  
177 route de Saint-Bel  
69811  
TASSIN CEDEX  
France**

Identified by the number :

**0082**

Made on the : **05/08/2004**

at : **Vierzon**

Division : **Fall Protection**

By : **Frederic GUICHARD**

[click address to go to....](#)