



ENGLISH

Datasheet

## RS Pro Fitting, 15mm Tube Inlet Port

RS Stock No: **511-3937**



### Product Details

RS Pro fitting has 15 mm tube inlet port. It withstands outlet pressure up to 15 bar. This fitting offers connection through 1/2 Inch BSP threaded port. It also accepts 15 mm compression fittings.

### Features and Benefits

- Polysulphone bodied flowmeters
- Open collector (NPN) pulse output proportional to flow rate
- Non-metallic fittings, PVDF, available for pure water or aggressive chemicals
- Robust sapphire bearings
- Traceable calibration certificate
- Hall effect detection suitable for used with opaque liquids

**Specifications:**

|                                 |                      |
|---------------------------------|----------------------|
| Body Material                   | PSU                  |
| Inlet Port Type                 | Tube                 |
| Outlet Port Type                | Threaded             |
| Threaded Outlet Port            | BSP 1/2 in           |
| Threaded Outlet Thread Gender   | Male                 |
| Threaded Outlet Thread Standard | BSP                  |
| Maximum Outlet Pressure         | 15 bar               |
| Tube Inlet Port                 | 15 mm                |
| Threaded Outlet Thread Size     | 1/2 in               |
| Type                            | Non-Metallic Fitting |
| Flow Rate                       | 2.5 to 30 l/min      |
| Length                          | 124 mm               |
| Maximum Temperature             | +125°C               |
| Minimum Temperature             | -25°C                |
| Operating Temperature Range     | -25 to +125°C        |