

## ERbic CAN Bus

### Ordering Information

ERbic Type	Color	Cable outlet	D-Sub 9-pin	Screw	Preferred <sup>1)</sup>	Part Number
<b>CAN Bus with external switch and cage clamp</b>						
CAN Bus with shield decoupling capacitor HLG*	anthracit	horizontal	Female	#4/40 UNC	yes	<b>144744</b>
CAN Bus with shield decoupling capacitor and service/PU connection HLG*	anthracit	horizontal	Female and Male (PU connection)	#4/40 UNC	yes	<b>154826</b>
<b>CAN Bus with external switch and screw terminal</b>						
CAN Bus Standard HLG*	anthracit	vertical	Female	#4/40 UNC	yes	<b>154824</b>
<b>CAN Bus with external switch, screw terminal and metal housing</b>						
CAN Bus MAX Standard HLG*	silver	axial	Female	#4/40 UNC	yes	<b>154039</b>
<b>CAN Bus node with screw terminal</b>						
CAN Bus Standard	anthracit	horizontal	Female	#4/40 UNC	yes	<b>103668</b>
CAN Bus with service/PU connection	anthracit	horizontal	Female and Male (PU connection)	#4/40 UNC		<b>134149</b>
CAN Bus with shield decoupling capacitor	anthracit	horizontal	Female	#4/40 UNC		<b>103642</b>
CAN Bus with shield decoupling capacitor, reversed	anthracit	horizontal	Female	#4/40 UNC		<b>104320</b>
CAN Bus with shield decoupling capacitor HLG*	anthracit	horizontal	Female	#4/40 UNC	yes	<b>124620</b>
CAN Bus with shield decoupling capacitor HLG*, reversed	anthracit	horizontal	Female	#4/40 UNC	yes	<b>124654</b>
CAN Bus Standard	anthracit	vertical	Female	#4/40 UNC		<b>103669</b>
CAN Bus with shield decoupling capacitor and service/PU connection	anthracit	horizontal	Female and Male (PU connection)	#4/40 UNC		<b>103662</b>
CAN Bus with shield decoupling capacitor	anthracit	vertical	Female	#4/40 UNC	yes	<b>103652</b>