



Sample photo

Order symbol: AL 232018
Product nbr: 7011360
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004239
El. number:
Finland: 3423633
Denmark: 8212004799
Italy: 7321090
Sweden: 2536335

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		230	200	180	Ingress Protection (EN 60529): IP 66/67
inch:		9.1	7.9	7.1	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:	Aluminium				Certificates: Underwriters Laboratories UL Canada Gost R
Base colour:	RAL 7001				
Cover colour:	RAL 7001				
Cover screws material:	Stainless steel				
Gasket material:	Neoprene				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 2320	Mounting plate				
ARH 2320	DIN-35 Mounting rail				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

