

Titan 385

DESCRIPTION AND GENERAL PROPERTIES

- Material Nitrile
- Length (cm) 24-26
- Thickness (mm) 1.40
- Wrist Safety cuff
- Colour/Color Blue
- Interior finish Textile support
- Exterior finish Ventilated back
- Size / EAN 9 10
- Packaging 10 pairs/bag - 100 pairs/carton



PERFORMANCE RESULTS

Certification category 2




4111X

Legends


EN 388 MECHANICAL HAZARDS



PERFORMANCE LEVELS

EN 407 THERMAL RISKS
heat and fire

PERFORMANCE LEVELS



CHEMICAL RISKS

EN ISO 374-1



Type A

U V W X Y Z

- A Methanol
B Acetone
C Acetonitrile
D Dichloromethane
E Carbon Disulfide
F Toluene
G Diethylamine
H Tetrahydrofurane
I Ethyl acetate

EN ISO 374-1



Type B

X Y Z

- J n-Heptane
K Sodium hydroxide 40%
L Sulphuric acid 96%
M Nitric acid 65%
N Acetic acid 99%
O Ammonia 25%
P Hydrogen peroxide 30%
S Hydrofluoric acid 40%
T Formaldehyde 37%

EN ISO 374-1



Type C



CUT

CUT RESISTANCE

- A1 ≥ 200 G A4 ≥ 1500 G A7 ≥ 4000 G
A2 ≥ 500 G A5 ≥ 2200 G A8 ≥ 5000 G
A3 ≥ 1000 G A6 ≥ 3000 G A9 ≥ 6000 G

MICRO-ORGANISMS

EN ISO 374-5



Protection against bacteria, fungi

EN ISO 374-5



Protection against bacteria, fungi, virus


VIRUS

EN 511



GOLD HAZARDS

PERFORMANCE LEVELS



EN 421



RADIOACTIVE CONTAMINATION

For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONNEL

SPECIFIC ADVANTAGES

- Freedom of movement: exceptionally comfortable textile support (no seams on the working surfaces)
- Excellent resistance to oils and greases
- Longer service life: quality of textile support and nitrile coating

MAIN FIELDS OF USE**Other industries**

- Household waste collection
- Forestry

Mechanical industry

- Metal shearing or cutting
 - Handling of thick, untrimmed sheet metal (not sharp-edged)
- Local Authorities (Waste Collection and Processing)**
- Waste collection

INSTRUCTIONS FOR USE**Instructions for use**

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the « CE »-type-tests.
- It is not recommended for persons sensitized to dithiocarbamates to use these gloves.
- Put the gloves on dry, clean hands.
- Rub over the gloves stained with oil or grease before taking them off.

Storage conditions

Store the gloves in their original packaging protected from light and humidity.

Laundering conditions

Caution : using the gloves or submitting them to cleaning or laundering process which is not specifically recommended can alter their performance levels.

Drying conditions

Ensure the inside of the gloves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/10/17/1480

- Issued by the notified body nr

0075

C.T.C

4 rue Herman FRENKEL

F - 69367 LYON CEDEX 07