




























- Standard hood and housing
- Corrosion-resistant hood and housing (series K)



Locking clip on housing
Locking bayonet on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm
Hood side entry standard construction  top entry  	42.32.32.08 42.32.32.81 42.32.32.71	29	29	29	HB.32.STS.1.29 HB.32.STS.1.29.Z HB.32.STS.1.29.G	      Panel cut-out     
	51.42.32.32.09 51.42.32.32.81 51.42.32.32.71	29	29	29	HB-K.32.STS.1.29 HB-K.32.STS.1.29.Z HB-K.32.STS.1.29.G	
	42.30.32.08 42.30.32.81 42.30.32.71	29	29	29	HB.32.STO.1.29 HB.32.STO.1.29.Z HB.32.STO.1.29.G	
	51.42.30.32.09 51.42.30.32.81 51.42.30.32.71	29	29	29	HB-K.32.STO.1.29 HB-K.32.STO.1.29.Z HB-K.32.STO.1.29.G	
Surface-mounted housing bottom entry  	42.50.32.00				HB.32.AG-VS	  Panel cut-out     
	51.42.50.32.00				HB-K.32.AG-VS	
Surface-mounted housing side entry  	42.60.32.47 42.60.32.81 42.60.32.48 42.60.32.97	29 2x29	29 2x29		HB.32.SG-VS.1.29 HB.32.SG-VS.1.29.Z HB.32.SG-VS.2.29 HB.32.SG-VS.2.29.Z	  Panel cut-out     
	51.42.60.32.09 51.42.60.32.81 51.42.60.32.48 51.42.60.32.97	29 2x29	29 2x29		HB-K.32.SG-VS.1.29 HB-K.32.SG-VS.1.29.Z HB-K.32.SG-VS.2.29 HB-K.32.SG-VS.2.29.Z	
Cable-to-cable hood bottom entry standard construction 	42.70.32.24 42.70.32.81 42.70.32.71	29	29	29	HB.32.KDO-VS.1.29 HB.32.KDO-VS.1.29.Z HB.32.KDO-VS.1.29.G	