

Datasheet

**RS Pro Zinc Plated Steel Adjustable Height Mount 68mm
Rubber 95mm 35mm 125mm 250kg 100mm M10 3.5°
RS Stock No: 283-1755**



Product Details

RS Pro adjustable height mount is a zinc plated steel machine mount, which is suitable for use in less demanding environments. It is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. It has a thread size of M10 and diameter of 68 mm. The foot material of mount is made from rubber and has an adjustable height from 35 to 95 mm. It has a static load capacity of 250 kg and a thread length of 100 mm with a tilt angle of 3.5°.

Features and Benefits

- Long bolt offers height adjustment
- Compensates with up to 7° swivel
- For use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery
- Built in levelling bolt means the stainless steel mounts can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability

**Specifications:**

Base Material	Zinc Plated Steel
Diameter	68 mm
Foot Material	Rubber
Maximum Adjustment Height	95 mm
Minimum Adjustment Height	35 mm
Overall Height	125 mm
Static Load Capacity	250 kg
Thread Length	100 mm
Thread Size	M10
Tilt Angle	3.5°